

FERN-0N-0A Cut Sheet



Photoelectric sensor, rectangular, polarized retroreflective, visible red light emission, 1-4m sensing distance, selectable light-on/dark-on, NPN, adjustable, 3-wire, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FERN-0N-0A>

Technical Specifications

Item	Photoelectric sensor
Shape	Rectangular
IP Rating	IP67
Sensing Method	Polarized retroreflective
Number of Wires	3
Switching Output	NPN
Sensing Distance	1-4m
Sensitivity	Adjustable
Operation Mode	Selectable light-on/dark-on
Switching Frequency	1 kHz
Light Emission	Visible red
Cable Length	6.5ft/2m
Connection	Pigtail
Conductor Size	25 AWG

Agency Approvals

UL Listed File #	None
UL Recognized File #	E224302
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document