

FF13PD24ZN Cut Sheet



Fandis Virdis series intake fan, side mount, 59 CFM, 24 VDC operating voltage, G3 (coarse) filter mat, NEMA 12, indoor use only, 6.97 x 6.97in enclosure cutout, ANSI 61 gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FF13PD24ZN>

Technical Specifications

Brand	Fandis
Series	Virdis series
Airflow Direction	Intake
Item	Fan
Mounting	Side
With Air Flaps	No
Filter Media	G3 (coarse) filter mat
Free Airflow	59 CFM
Airflow with Grill and Filter(s)	45 CFM
Operating Voltage	24 VDC
Power Consumption	8W

Current Draw	342 mA
Electrical Connection	Screwless terminal block
Maximum Static Pressure	62Pa
Operating Temperature	14 to 131 deg F
Average Noise Level	42 dBA
NEMA Rating	12
Application	Indoor use only
IP Rating	IP54
Enclosure Cutout	6.97 x 6.97in
Color	ANSI 61 gray
Additional Information	Purchase exhaust grille separately

Agency Approvals

UL Listed File #	E500932
UL Recognized File #	E237844
UL Hazardous File #	None
CE	View CE declarations
CSA File #	260922
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/FF13PD24ZN.pdf>
See store item page for other formats.