

# FF15D24ZF Cut Sheet



Fandis Virdis series intake fan, side mount, 175 CFM, 24 VDC operating voltage, G3 (coarse) filter mat, NEMA 12, indoor use only, 8.78 x 8.78in enclosure cutout, ANSI 61 gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FF15D24ZF>

## Technical Specifications

|   |                                    |
|---|------------------------------------|
| <b>Brand</b>                            | Fandis                             |
| <b>Series</b>                           | Virdis series                      |
| <b>Airflow Direction</b>                | Intake                             |
| <b>Item</b>                             | Fan                                |
| <b>Mounting</b>                         | Side                               |
| <b>With Air Flaps</b>                   | No                                 |
| <b>Filter Media</b>                     | G3 (coarse) filter mat             |
| <b>Free Airflow</b>                     | 175 CFM                            |
| <b>Airflow with Grill and Filter(s)</b> | 118 CFM                            |
| <b>Operating Voltage</b>                | 24 VDC                             |
| <b>Power Consumption</b>                | 31W                                |
| <b>Current Draw</b>                     | 1.30A                              |
| <b>Electrical Connection</b>            | Screwless terminal block           |
| <b>Maximum Static Pressure</b>          | 156Pa                              |
| <b>Operating Temperature</b>            | 14 to 131 deg F                    |
| <b>Average Noise Level</b>              | 60 dBA                             |
| <b>NEMA Rating</b>                      | 12                                 |
| <b>Application</b>                      | Indoor use only                    |
| <b>IP Rating</b>                        | IP54                               |
| <b>Enclosure Cutout</b>                 | 8.78 x 8.78in                      |
| <b>Color</b>                            | ANSI 61 gray                       |
| <b>Additional Information</b>           | Purchase exhaust grille separately |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E500932                                |
| <b>UL Recognized File #</b> | E237844                                |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | 260922                                 |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |