

FFI7-0P-1E Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, diffuse, infrared, 400mm sensing distance, selectable light-on/dark-on, PNP, teach-in button, 500 Hz switching frequency, 316L stainless steel housing, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FFI7-0P-1E>

Technical Specifications

Brand	AutomationDirect
Item	Photoelectric sensor
Shape	Tubular
Barrel Type	Threaded
Housing Size	18mm diameter x 82.5mm body
IP Rating	IP69K
Application	For harsh duty / food and beverage applications
Housing Material	316L stainless steel
Sensing Method	Diffuse
Operating Voltage	10-30 VDC

Number of Wires	4
Switching Output	PNP
Sensing Distance	400mm
Sensitivity	Teach-in button
Operation Mode	Selectable light-on/dark-on
Switching Frequency	500 Hz
Light Emission (NP)	Infrared
Connection	4-pin M12 quick-disconnect
Includes	Mounting hardware
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E187310
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FFI7-0P-1E.pdf>
See store item page for other formats.