## FFIZ-0N-1E Cut Sheet





AutomationDirect photoelectric sensor, tubular, threaded, 316L stainless steel housing, through-beam receiver, 20m sensing distance, 10-30 VDC operating voltage, selectable light-on/dark-on, NPN, 4-wire, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



https://www.automationdirect.com/pn/FFIZ-0N-1E

## **Technical Specifications**

Brand	AutomationDirect
Item	Photoelectric sensor
Shape	Tubular
Barrel Type	Threaded
Housing Size	18mm diameter x 82.5mm body
IP Rating	IP69K
Application	For harsh duty / food and beverage applications
Housing Material	316L stainless steel
Sensing Method	Through-beam receiver

Operating Voltage	10-30 VDC
Number of Wires	4
Switching Output	NPN
Sensing Distance	20m
Operation Mode	Selectable light-on/dark-on
Switching Frequency	250 Hz
Connection	4-pin M12 quick-disconnect
Includes	Mounting hardware
Additional Information	Purchase cable separately

## Agency Approvals

E187310
None
None
View CE declarations
None
Yes (See CE Doc)
View EU REACH document

## Dimensional Drawings



2D Drawing PDF Link: https://cdn.automationdirect.com /static/drawings/FFIZ-0N-1E.pdf See store item page for other formats.