

# FG1P-100PP-28 Cut Sheet



ProSense oil mechanical flow meter, variable area, 1in male NPT process connection, 4 to 28 GPM, 20 to 100 LPM.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FG1P-100PP-28>

## Technical Specifications

Brand	ProSense
Item	Mechanical flow meter
Media Type	Oil
Sensing Type	Variable area
Process Connection	1in male NPT
Measuring Range	4 to 28 GPM
Measuring Range 2	20 to 100 LPM

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/FG1P-100PP-28.pdf>  
See store item page for other formats.