

# FG1P-50BP-10 Cut Sheet



ProSense oil mechanical flow meter, variable area, 1/2in female NPT process connection, 1 to 10 GPM, 4 to 35 LPM.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FG1P-50BP-10>

---

## Technical Specifications

|                           |                       |
|---------------------------|-----------------------|
| <b>Brand</b>              | ProSense              |
| <b>Item</b>               | Mechanical flow meter |
| <b>Media Type</b>         | Oil                   |
| <b>Sensing Type</b>       | Variable area         |
| <b>Process Connection</b> | 1/2in female NPT      |
| <b>Measuring Range</b>    | 1 to 10 GPM           |
| <b>Measuring Range 2</b>  | 4 to 35 LPM           |

---

## Agency Approvals

|                             |                                        |
|-----------------------------|----------------------------------------|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

---

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/FG1P-50BP-10.pdf>  
See store item page for other formats.