

FG1P-75BP-2 Cut Sheet



ProSense oil mechanical flow meter, variable area, 3/4 in male NPT process connection, 0.25–2.5 GPM, 1–10 LPM.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FG1P-75BP-2>

Technical Specifications

Brand	ProSense
Item	Mechanical flow meter
Media Type	Oil
Sensing Type	Variable area
Process Connection	3/4 in male NPT
Measuring Range	0.25–2.5 GPM
Measuring Range 2	1–10 LPM
Seal Material	Buna-N
Wetted Parts	Stainless steel, brass, polysulfone (PSU), Buna-N

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FG1P-75BP-2.pdf>
See store item page for other formats.