

# FG1W-100PP-16 Cut Sheet



ProSense water mechanical flow meter, variable area, 1in male NPT process connection, 1 to 16 GPM, 5 to 60 LPM.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FG1W-100PP-16>

## Technical Specifications

|                    |                       |
|--------------------|-----------------------|
| Brand              | ProSense              |
| Item               | Mechanical flow meter |
| Media Type         | Water                 |
| Sensing Type       | Variable area         |
| Process Connection | 1in male NPT          |
| Measuring Range    | 1 to 16 GPM           |
| Measuring Range 2  | 5 to 60 LPM           |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/FG1W-100PP-16.pdf>  
See store item page for other formats.