

# FG1W-100PP-28 Cut Sheet



ProSense water mechanical flow meter, variable area, 1in male NPT process connection, 4 to 28 GPM, 20 to 100 LPM.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FG1W-100PP-28>

---

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Mechanical flow meter
<b>Media Type</b>	Water
<b>Sensing Type</b>	Variable area
<b>Process Connection</b>	1in male NPT
<b>Measuring Range</b>	4 to 28 GPM
<b>Measuring Range 2</b>	20 to 100 LPM

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>