

FG1W-100PP-4 Cut Sheet



ProSense water mechanical flow meter, variable area, 1in male NPT process connection, 0.5 to 4 GPM, 2 to 15 LPM.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FG1W-100PP-4>

Technical Specifications

| | |
|--------------------|-----------------------|
| Brand | ProSense |
| Item | Mechanical flow meter |
| Media Type | Water |
| Sensing Type | Variable area |
| Process Connection | 1in male NPT |
| Measuring Range | 0.5 to 4 GPM |
| Measuring Range 2 | 2 to 15 LPM |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FG1W-100PP-4.pdf>
See store item page for other formats.