

FG1W-50BP-10 Cut Sheet



ProSense water mechanical flow meter, variable area, 1/2in female NPT process connection, 1 to 10 GPM, 4 to 35 LPM.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FG1W-50BP-10>

Technical Specifications

| | |
|---------------------------|-----------------------|
| Brand | ProSense |
| Item | Mechanical flow meter |
| Media Type | Water |
| Sensing Type | Variable area |
| Process Connection | 1/2in female NPT |
| Measuring Range | 1 to 10 GPM |
| Measuring Range 2 | 4 to 35 LPM |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |