

FG1W-75BP-10 Cut Sheet



ProSense water mechanical flow meter, variable area, 3/4in male NPT process connection, 1 to 10 GPM, 4 to 35 LPM.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FG1W-75BP-10>

Technical Specifications

Brand	ProSense
Item	Mechanical flow meter
Media Type	Water
Sensing Type	Variable area
Process Connection	3/4in male NPT
Measuring Range	1 to 10 GPM
Measuring Range 2	4 to 35 LPM

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FG1W-75BP-10.pdf>
See store item page for other formats.