

# FG1W-75BP-18 Cut Sheet



ProSense water mechanical flow meter, variable area, 3/4in male NPT process connection, 3 to 18 GPM, 15 to 65 LPM.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FG1W-75BP-18>

## Technical Specifications

Brand	ProSense
Item	Mechanical flow meter
Media Type	Water
Sensing Type	Variable area
Process Connection	3/4in male NPT
Measuring Range	3 to 18 GPM
Measuring Range 2	15 to 65 LPM

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/FG1W-75BP-18.pdf>  
See store item page for other formats.