

# FG1W-75BP-2 Cut Sheet



ProSense water mechanical flow meter, variable area, 3/4in male NPT process connection, 0.25 to 2.5 GPM, 1 to 10 LPM.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FG1W-75BP-2>

## Technical Specifications

|                    |                       |
|--------------------|-----------------------|
| Brand              | ProSense              |
| Item               | Mechanical flow meter |
| Media Type         | Water                 |
| Sensing Type       | Variable area         |
| Process Connection | 3/4in male NPT        |
| Measuring Range    | 0.25 to 2.5 GPM       |
| Measuring Range 2  | 1 to 10 LPM           |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/FG1W-75BP-2.pdf>  
See store item page for other formats.