

FG1W-75BP-4 Cut Sheet



ProSense water mechanical flow meter, variable area, 3/4in male NPT process connection, 0.5 to 4 GPM, 2 to 15 LPM.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FG1W-75BP-4>

Technical Specifications

Brand	ProSense
Item	Mechanical flow meter
Media Type	Water
Sensing Type	Variable area
Process Connection	3/4in male NPT
Measuring Range	0.5 to 4 GPM
Measuring Range 2	2 to 15 LPM

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document