

FL06 Cut Sheet



PBC Simplicity series closed plain bearing, PTFE, 3/8in inside diameter, 5/8in outside diameter, 7/8in overall length, 0.0005in running clearance. For use with 3/8in diameter PBC shafts.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FL06>

Technical Specifications

Brand	PBC
Item	Plain bearing
Series	Simplicity
Bearing Type	Closed
Bearing Material	PTFE
Bearing Inside Diameter	3/8in
Bearing Outside Diameter	5/8in
Overall Length	7/8in
Flanged	No
Running Clearance	0.0005in
For Use With	3/8in diameter PBC shafts

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/FL06.pdf>
See store item page for other formats.