

FLHTF200A115 Cut Sheet



Hammond enclosure heater, axial fan, 200W heating capacity, incoloy tubular heating element, 120 VAC operating voltage, 60 Hz, adjustable thermostat, N.C. (open on rise) 0 to 100 deg F, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLHTF200A115>

Technical Specifications

Brand	Hammond
Item	Enclosure heater
Fan Type	Axial
Heating Capacity	200W
Heating Element	Incoloy tubular
Operating Voltage	120 VAC
Hertz	60 Hz
Connection	3-pole terminal block for 12 AWG max solid or stranded wire
Heater Control	Adjustable thermostat
Contact 1	N.C. (open on rise) 0 to 100 deg F
Switching Differential	13 deg F
Switching Tolerance	+/-5 deg F
Mounting	Panel

Agency Approvals

UL Listed File #	E331157
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	LR43697
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	RoHS Statement