

# FLL-A1206USTB Cut Sheet



Fandis Lumeis LED enclosure light, 115 VAC operating voltage, on/off switch, 14in length, 600 lm, screw mount, 2-pole dual cage clamp for 20-14 AWG stranded or solid wire, 5W, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLL-A1206USTB>

## Technical Specifications

<b>Brand</b>	Fandis
<b>Item</b>	LED enclosure light
<b>Series</b>	Lumeis
<b>Operating Voltage</b>	115 VAC
<b>Switch Type</b>	On/off
<b>Length</b>	14in
<b>Luminous Flux</b>	600 lm
<b>Color Temperature</b>	6000K
<b>Beam Angle</b>	120 degrees

<b>Integral Receptacle</b>	No
<b>Mounting</b>	Screw
<b>Connection</b>	2-pole dual cage clamp for 20-14 AWG stranded or solid wire
<b>Power Consumption</b>	5W
<b>IP Rating</b>	IP20
<b>Rotatable</b>	Yes
<b>Requires</b>	M4.8 mounting screws

## Agency Approvals

<b>UL Recognized File #</b>	UL E237844
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/FLL-A1206USTB.pdf>  
See store item page for other formats.