

FLL-C3006UITM Cut Sheet



Fandis Lumeis LED enclosure light, 20–265 VAC/VDC operating voltage, motion sensor switch, 14in length, 600 lm, magnet mount, 2-pole dual cage clamp for 20-14 AWG stranded or solid wire, 5W, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLL-C3006UITM>

Technical Specifications

Brand	Fandis
Item	LED enclosure light
Series	Lumeis
Operating Voltage	20–265 VAC/VDC
Switch Type	Motion sensor
Length	14in
Luminous Flux	600 lm
Color Temperature	6000K

Beam Angle	120 degrees
Integral Receptacle	No
Mounting	Magnet
Connection	2-pole dual cage clamp for 20-14 AWG stranded or solid wire
Power Consumption	5W
IP Rating	IP20
Rotatable	Yes

Agency Approvals

UL Recognized File #	UL E237844
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/FLL-C3006UITM.pdf>
See store item page for other formats.