

FLL-C3006USTB Cut Sheet



Fandis Lumeis LED enclosure light, 20–265 VAC/VDC operating voltage, on/off switch, 14in length, 600 lm, screw mount, 2-pole dual cage clamp for 20-14 AWG stranded or solid wire, 5W, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLL-C3006USTB>

Technical Specifications

Brand	Fandis
Item	LED enclosure light
Series	Lumeis
Operating Voltage	20–265 VAC/VDC
Switch Type	On/off
Length	14in
Luminous Flux	600 lm
Color Temperature	6000K
Beam Angle	120 degrees

Integral Receptacle	No
Mounting	Screw
Connection	2-pole dual cage clamp for 20-14 AWG stranded or solid wire
Power Consumption	5W
IP Rating	IP20
Rotatable	Yes
Requires	M4.8 mounting screws

Agency Approvals

UL Recognized File #	UL E237844
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/FLL-C3006USTB.pdf>
See store item page for other formats.