

# FLL-C3006USTM Cut Sheet



Fandis Lumeis LED enclosure light, 20–265 VAC/VDC operating voltage, on/off switch, 14in length, 600 lm, magnet mount, 2-pole dual cage clamp for 20-14 AWG stranded or solid wire, 5W, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLL-C3006USTM>

## Technical Specifications

<b>Brand</b>	Fandis
<b>Item</b>	LED enclosure light
<b>Series</b>	Lumeis
<b>Operating Voltage</b>	20–265 VAC/VDC
<b>Switch Type</b>	On/off
<b>Length</b>	14in
<b>Luminous Flux</b>	600 lm
<b>Color Temperature</b>	6000K

<b>Beam Angle</b>	120 degrees
<b>Integral Receptacle</b>	No
<b>Mounting</b>	Magnet
<b>Connection</b>	2-pole dual cage clamp for 20-14 AWG stranded or solid wire
<b>Power Consumption</b>	5W
<b>IP Rating</b>	IP20
<b>Rotatable</b>	Yes

## Agency Approvals

<b>UL Recognized File #</b>	UL E237844
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/FLL-C3006USTM.pdf>  
See store item page for other formats.