

FLN08 Cut Sheet



PBC Simplicity series open plain bearing, PTFE, 1/2in inside diameter, 7/8in outside diameter, 1-1/4in overall length, 0.0005in running clearance. For use with 1/2in diameter PBC shafts.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLN08>

Technical Specifications

Brand	PBC
Item	Plain bearing
Series	Simplicity
Bearing Type	Open
Bearing Material	PTFE
Bearing Inside Diameter	1/2in
Bearing Outside Diameter	7/8in
Overall Length	1-1/4in
Flanged	No
Running Clearance	0.0005in
For Use With	1/2in diameter PBC shafts

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/FLN08.pdf>
See store item page for other formats.