

FLS-BM-100 Cut Sheet



ProSense float liquid level switch, horizontal side mount, 2.11in insertion length, 1.0in diameter float, polypropylene, 316 stainless steel wetted parts, -40 to 221 deg F, 3/8-24 male UNC with nut process connection, SPST reed switch, N.O./N.C. selectable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLS-BM-100>

Technical Specifications

Brand	ProSense
Item	Level switch
Sensor Type	Float
Media Type	Liquid
Mounting	Horizontal side
Insertion Length	2.11in
Float	1.0in diameter
Process Connection	3/8-24 male UNC with nut
Wetted Parts	Polypropylene, 316 stainless steel
Process Temperature	-40 to 221 deg F
Output	SPST reed switch, N.O./N.C. selectable
Electrical Connection	24in 22AWG lead wires with stripped ends
Conductor Insulation Material	316L stainless steel

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FLS-BM-100.pdf>
See store item page for other formats.