

# FLS-HL-200 Cut Sheet



ProSense float liquid level switch, horizontal side mount, 3.19in insertion length, 1.0in diameter float, 316 stainless steel wetted parts, -40 to 392 deg F, 1/2-13 male UNC with washers and nut process connection, SPST reed switch, N.O./N.C. selectable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLS-HL-200>

## Technical Specifications

Brand	ProSense
Item	Level switch
Sensor Type	Float
Media Type	Liquid
Mounting	Horizontal side
Insertion Length	3.19in
Float	1.0in diameter
Process Connection	1/2-13 male UNC with washers and nut
Wetted Parts	316 stainless steel
Process Temperature	-40 to 392 deg F
Output	SPST reed switch, N.O./N.C. selectable
Electrical Connection	24in 22AWG lead wires with stripped ends
Conductor	316L stainless steel
Insulation Material	

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E320431
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/FLS-HL-200.pdf>  
See store item page for other formats.