

FLS-HM-400 Cut Sheet



ProSense float liquid level switch, horizontal side mount, 4.6in insertion length, 0.63in diameter float, 316 stainless steel wetted parts, -40 to +392 °F, 1in male NPT process connection, SPST reed switch, N.O./N.C. selectable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLS-HM-400>

Technical Specifications

Brand	ProSense
Item	Level switch
Sensor Type	Float
Media Type	Water, oil and chemicals
Mounting	Horizontal side
Insertion Length	4.6in
Float	0.63in diameter
Process Connection	1in male NPT
Wetted Parts	316 stainless steel
Process Temperature	-40 to +392 °F
Output	SPST reed switch, N.O./N.C. selectable
Electrical Connection	24in 22 AWG lead wires with stripped ends
Conductor Insulation Material	316L stainless steel

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	E366154
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/FLS-HM-400.pdf>
See store item page for other formats.