

FLS-VD-500 Cut Sheet



ProSense float liquid level switch, vertical top mount, 32in insertion length, 0.9in diameter float, 316 stainless steel wetted parts, -40 to 302 deg F, 3/4in male NPT pipe plug process connection, SPST reed switch, N.C.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLS-VD-500>

Technical Specifications

| | |
|------------------------|--------------------------------------|
| Brand | ProSense |
| Item | Level switch |
| Sensor Type | Float |
| Media Type | Liquid |
| Mounting | Vertical top |
| Insertion Length | 32in |
| Float | 0.9in diameter |
| Process Connection | 3/4in male NPT pipe plug |
| Wetted Parts | 316 stainless steel |
| Process Temperature | -40 to 302 deg F |
| Output | SPST reed switch, N.C. |
| Electrical Connection | 72in cable with 22AWG conductors |
| Jacket Material | Halar |
| Additional Information | Low level switch for 55 gallon drums |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/FLS-VD-500.pdf>
See store item page for other formats.