

FLS-VL-900 Cut Sheet



ProSense float liquid level switch, suspendible/submersible mount, 1.44in diameter slosh shield float, Buna-N, brass, polybutylene, halar wetted parts, -40 to 221 deg F, SPST reed switch, N.O./N.C. selectable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLS-VL-900>

Technical Specifications

Brand	ProSense
Item	Level switch
Sensor Type	Float
Media Type	Liquid
Mounting	Suspendible/submersible
Float	1.44in diameter slosh shield
Wetted Parts	Buna-N, brass, polybutylene, halar
Process Temperature	-40 to 221 deg F
Output	SPST reed switch, N.O./N.C. selectable
Electrical Connection	20ft (6m) cable with 22AWG conductors
Jacket Material	Halar
Additional Information	Not for use in hot water at temperatures above 149 deg F (65 deg C)

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document