

FLS-VM-200 Cut Sheet



ProSense float liquid level switch, vertical top mount, 1.63in insertion length, 1.0in diameter float, Buna-N, polybutylene wetted parts, -40 to 221 deg F, 1/8in male NPT process connection, SPST reed switch, N.O./N.C. selectable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLS-VM-200>

Technical Specifications

Brand	ProSense
Item	Level switch
Sensor Type	Float
Media Type	Liquid
Mounting	Vertical top
Insertion Length	1.63in
Float	1.0in diameter
Process Connection	1/8in male NPT

Wetted Parts	Buna-N, polybutylene
Process Temperature	-40 to 221 deg F
Output	SPST reed switch, N.O./N.C. selectable
Electrical Connection	24in 22AWG lead wires with stripped ends
Conductor Insulation Material	316L stainless steel
Additional Information	Not for use in hot water at temperatures above 149 deg F (65 deg C)

Agency Approvals

UL Listed File #	None
UL Recognized File #	E320431
UL Hazardous File #	None
CE	View CE declarations
CSA File #	259726
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FLS-VM-200.pdf>
See store item page for other formats.