

FLS-VM-800 Cut Sheet



ProSense float liquid level switch, vertical top mount, 1.99in insertion length, 0.875in diameter float, polypropylene wetted parts, -40 to 140 deg F, 3/4in PVC pipe insert process connection, SPST reed switch, N.C.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLS-VM-800>

Technical Specifications

Brand	ProSense
Item	Level switch
Sensor Type	Float
Media Type	Liquid
Mounting	Vertical top
Insertion Length	1.99in
Float	0.875in diameter
Process Connection	3/4in PVC pipe insert
Wetted Parts	Polypropylene
Process Temperature	-40 to 140 deg F
Output	SPST reed switch, N.C.
Electrical Connection	24in 22AWG lead wires with stripped ends
Conductor Insulation Material	PVC
Additional Information	HVAC condensate level switch

Agency Approvals

UL Listed File #	None
UL Recognized File #	E320431
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document