

FLS-VS-200 Cut Sheet



ProSense float liquid level switch, vertical top mount, 1.25in insertion length, 0.58in diameter float, polypropylene wetted parts, -40 to 221 deg F, 1/8in male NPT process connection, SPST reed switch, N.C.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FLS-VS-200>

Technical Specifications

Brand	ProSense
Item	Level switch
Sensor Type	Float
Media Type	Liquid
Mounting	Vertical top
Insertion Length	1.25in
Float	0.58in diameter
Process Connection	1/8in male NPT
Wetted Parts	Polypropylene
Process Temperature	-40 to 221 deg F
Output	SPST reed switch, N.C.
Electrical Connection	24in 22AWG lead wires with stripped ends
Conductor	316L stainless steel
Insulation Material	

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FLS-VS-200.pdf>
See store item page for other formats.