

FMM200-1001 Cut Sheet



ProSense liquid flow meter, magnetic-inductive, 2in female NPT process connection, 0 to 160 GPM, -4 to 176 deg F, 0.02 to 80,000,000 gallons, Output: switch, pulse or frequency, Output 2: switch, analog or reset input.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FMM200-1001>

Technical Specifications

Brand	ProSense
Item	Flow meter
Media Type	Liquid
Sensing Type	Magnetic-inductive
Process Connection	2in female NPT
Measuring Range	0 to 160 GPM
Measuring Range 2	-4 to 176 deg F
Measuring Range 3	0.02 to 80,000,000 gallons

Output	Switch (N.O./N.C.) or pulse or frequency, PNP/NPN selectable
Output 2	Switch (N.O./N.C.) or analog or reset input, PNP/NPN selectable or 4-20 mA/0-10 VDC
Operating Voltage	18-32 VDC
Electrical Connection	4-pin M12 quick-disconnect
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E320431
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FMM200-1001.pdf>
See store item page for other formats.