

# FMM50-1001 Cut Sheet



ProSense liquid flow meter, magnetic-inductive, 1/2in female NPT process connection, 0 to 6.6 GPM, -4 to 176 F, 0.01 to 30,000,000 Gallons, Output: switch or pulse, Output 2: switch, analog or reset input, 19 to 30 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FMM50-1001>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Flow meter
<b>Media Type</b>	Liquid
<b>Sensing Type</b>	Magnetic-inductive
<b>Process Connection</b>	1/2in female NPT
<b>Measuring Range</b>	0 to 6.6 GPM
<b>Measuring Range 2</b>	-4 to 176 F
<b>Measuring Range 3</b>	0.01 to 30,000,000 Gallons
<b>Output</b>	Switch (N.O./N.C.) or pulse, PNP/NPN selectable
<b>Output 2</b>	Switch (N.O./N.C.) or analog or reset input, PNP/NPN selectable or 4-20 mA/0-10 VDC
<b>Operating Voltage</b>	19 to 30 VDC
<b>Electrical Connection</b>	4-pin M12 quick-disconnect
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	E320431
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/FMM50-1001.pdf>  
See store item page for other formats.