

FMM50-1002 Cut Sheet



ProSense liquid flow meter, magnetic-inductive, 1/2in female NPT process connection, 0 to 6.6 GPM, -4 to 176 F, Output: analog, Output 2: analog, 20 to 30 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FMM50-1002>

Technical Specifications

| | |
|------------------------|----------------------------|
| Brand | ProSense |
| Item | Flow meter |
| Media Type | Liquid |
| Sensing Type | Magnetic-inductive |
| Process Connection | 1/2in female NPT |
| Measuring Range | 0 to 6.6 GPM |
| Measuring Range 2 | -4 to 176 F |
| Output | Analog, 4-20 mA |
| Output 2 | Analog, 4-20 mA |
| Operating Voltage | 20 to 30 VDC |
| Electrical Connection | 4-pin M12 quick-disconnect |
| Additional Information | Purchase cable separately |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E320431 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |