

FMM75-1002 Cut Sheet



ProSense liquid flow meter, magnetic-inductive, 3/4in female NPT process connection, 0 to 13.2 GPM, -4 to 176 deg F, Output: analog, Output 2: analog.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FMM75-1002>

Technical Specifications

Brand	ProSense
Item	Flow meter
Media Type	Liquid
Sensing Type	Magnetic-inductive
Process Connection	3/4in female NPT
Measuring Range	0 to 13.2 GPM
Measuring Range 2	-4 to 176 deg F
Output	Analog, 4-20 mA
Output 2	Analog, 4-20 mA
Operating Voltage	20-30 VDC
Electrical Connection	4-pin M12 quick-disconnect
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E320431
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FMM75-1002.pdf>
See store item page for other formats.