

FMRE-00-0A Cut Sheet



AutomationDirect photoelectric sensor, rectangular, 316L stainless steel housing, through-beam emitter, visible red, 10m sensing distance, 10-30 VDC operating voltage, 3-wire, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FMRE-00-0A>

Technical Specifications

Brand	AutomationDirect
Item	Photoelectric sensor
Shape	Rectangular
Housing Size	21 x 34.8 x 13mm
IP Rating	IP69K
Application	For harsh duty / food and beverage applications
Housing Material	316L stainless steel
Sensing Method	Through-beam emitter

Operating Voltage	10-30 VDC
Number of Wires	3
Sensing Distance	10m
Light Emission (NP)	Visible red
Cable Length	6.5ft/2m
Connection	Pigtail
Conductor Size	24 AWG

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FMRE-00-0A.pdf>
See store item page for other formats.