

FMX11-CA11DS06 Cut Sheet



Endress+Hauser Waterpilot hydrostatic submersible level transmitter, 0 to 0.2 bar (6.7ft of water column) sensing range, 4-20 mA, 22mm diameter housing, shielded and vented 6m (19.7ft) cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FMX11-CA11DS06>

Technical Specifications

Brand	Endress+Hauser
Item	Submersible level transmitter
Series	Waterpilot
Sensor Type	Hydrostatic
Sensing Range	0 to 0.2 bar (6.7ft of water column)
Mounting	Vertical suspension
Process Temperature	0 to 70 deg C
Output	4-20 mA
Operating Voltage	8-28 VDC
Housing Size	22mm diameter
Housing Material	Stainless steel
Electrical Connection	Shielded and vented 6m (19.7ft) cable
Jacket Material	TPE

Agency Approvals

UL Listed File #	E532645
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	NSF Listing

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/FMX11-CA11DS06.pdf>
See store item page for other formats.