

# FMX21-FE121HGB11A Cut Sheet



Endress+Hauser Waterpilot hydrostatic submersible level transmitter, 0 to 1 bar (33.5ft of water column) sensing range, 4-20 mA, 42mm diameter housing, shielded and vented 20m (65.6ft) cable, hazardous location rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FMX21-FE121HGB11A>

## Technical Specifications

<b>Brand</b>	Endress+Hauser
<b>Item</b>	Submersible level transmitter
<b>Series</b>	Waterpilot
<b>Sensor Type</b>	Hydrostatic
<b>Sensing Range</b>	0 to 1 bar (33.5ft of water column)
<b>Mounting</b>	Vertical suspension
<b>Process Temperature</b>	-10 to 70 deg C
<b>Output</b>	4-20 mA

<b>Operating Voltage</b>	10.5-35 VDC (non-hazardous areas), 10.5-30 VDC (hazardous areas)
<b>Housing Size</b>	42mm diameter
<b>Housing Material</b>	Stainless steel
<b>Electrical Connection</b>	Shielded and vented 20m (65.6ft) cable
<b>Jacket Material</b>	Low-density polyethylene (LDPE)
<b>Application</b>	Hazardous location rated

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	FM Approval and Control Drawing

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/FMX21-FE121HGB11A.pdf>  
See store item page for other formats.