

FMX21-FE121KGB15A Cut Sheet



Endress+Hauser Waterpilot hydrostatic submersible level transmitter, 0 to 2 bar (66.9 ft of water column) sensing range, 4-20 mA, 42mm diameter housing, shielded and vented 30m (98.4ft) cable, hazardous location rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FMX21-FE121KGB15A>

Technical Specifications

Brand	Endress+Hauser
Series	Waterpilot
Item	Submersible level transmitter
Sensor Type	Hydrostatic
Sensing Range	0 to 2 bar (66.9 ft of water column)
Output	4-20 mA
Operating Voltage	10.5-35 VDC (non-hazardous areas), 10.5-30 VDC (hazardous areas)
Housing Size	42mm diameter
Housing Material	Stainless steel
Electrical Connection	Shielded and vented 30m (98.4ft) cable
Jacket Material	Low-density polyethylene (LDPE)
Application	Hazardous location rated

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	FM Approval and Control Drawing