

FOS.2.2140R Cut Sheet



SapiSelco phosphorescent cable tie, 11.02in length, 0.18in width, 48.51lb tensile strength, 2.99in maximum bundle diameter, natural, nylon. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FOS.2.2140R>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	Phosphorescent
Length	11.02in
Width	0.18in
Tensile Strength	48.51lb
Maximum Bundle Diameter	2.99in
Color	Natural
Material	Nylon
UV Resistant	No
Temperature Rating	+23 to +140 deg F
Installation Temperature	+32 deg F
Flammability	UL 94 V-2
Quantity per Pack	100

Agency Approvals

CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document