

FR121006HW Cut Sheet



AttaBox Freedom series enclosure, NEMA 1/3/3S/4X/12/13, 12 x 10 x 6in (HxWxD), wall mount, fiberglass reinforced polyester, gray, crowned hinged screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FR121006HW>

Technical Specifications

Brand	AttaBox
Item	Enclosure
Series	Freedom
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	1/3/3S/4X/12/13
IP Rating	IP66
Nominal Enclosure Height	12in
Nominal Enclosure Width	10in
Nominal Enclosure Depth	6in
Mounting	Wall

Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Material	Fiberglass reinforced polyester
Color	Gray
Cover Type	Crowned hinged screw cover
Hinge Type	Molded hinges with stainless steel pins
Number of Hinges Per Door	2
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E64358, E362920
UL Recognized File #	E333478
UL Hazardous File #	none
CE	View CE declarations
CSA File #	LR069014
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FR121006HW.pdf>
See store item page for other formats.