

# FS14-14N-P Cut Sheet



HydroMode potable water push-to-connect fitting, female, straight, acetal body, acetal threads, (1) 1/4in tube to (1) 1/4in female NPT connection(s), NSF/ANSI 61. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FS14-14N-P>

## Technical Specifications

|                              |  |
|------------------------------|--|
| <b>Brand</b>                 | HydroMode                              |
| <b>Item</b>                  | Potable water Push-to-connect Fitting  |
| <b>Gender</b>                | Female                                 |
| <b>Fitting Type</b>          | Straight                               |
| <b>Body Material</b>         | Acetal                                 |
| <b>Thread Material</b>       | Acetal                                 |
| <b>Port Connection Info</b>  | (1) 1/4in tube to (1) 1/4in female NPT |
| <b>Operating Pressure</b>    | 145 psi                                |
| <b>Operating Temperature</b> | 32 to 158 deg F                        |
| <b>Agency Approval</b>       | NSF/ANSI 61                            |
| <b>Quantity per Pack</b>     | 5                                      |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |