

# FTI26-CA4MWDG Cut Sheet



Endress+Hauser Nivector capacitance bulk solids level switch, polycarbonate wetted parts, G1 male thread process connection, switch PNP, 3-wire, N.O./N.C. complementary, 4-pin M12 quick-disconnect, IP65 IP67 (NEMA 4X).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FTI26-CA4MWDG>

## Technical Specifications

<b>Brand</b>	Endress+Hauser
<b>Item</b>	Level switch
<b>Series</b>	Nivector
<b>Sensor Type</b>	Capacitance
<b>Media Type</b>	Bulk solids
<b>Mounting</b>	Any orientation
<b>Insertion Length</b>	2.84in/72mm
<b>Process Connection</b>	G1 male thread

<b>Process Temperature</b>	-4 to 176 deg F
<b>Output</b>	Switch PNP, 3-wire, N.O./N.C. complementary
<b>Operating Voltage</b>	12-30 VDC
<b>Wetted Parts</b>	Polycarbonate
<b>Electrical Connection</b>	4-pin M12 quick-disconnect
<b>Housing Rating</b>	IP65 IP67 (NEMA 4X)
<b>IO-Link Compatible</b>	No

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	053988_C_000
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/FTI26-CA4MWDG.pdf>  
See store item page for other formats.