

FTI26-CA4VWDG Cut Sheet



Endress+Hauser Nivector capacitance bulk solids level switch, polycarbonate wetted parts, G1 male thread process connection, switch PNP, 3-wire, N.O. or N.C., EN 175301-803-A connector, IP65, NEMA 4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FTI26-CA4VWDG>

Technical Specifications

Brand	Endress+Hauser
Item	Level switch
Series	Nivector
Sensor Type	Capacitance
Media Type	Bulk solids
Mounting	Any orientation
Insertion Length	2.84in/72mm
Process Connection	G1 male thread

Process Temperature	-4 to 176 deg F
Output	Switch PNP, 3-wire, N.O. or N.C.
Operating Voltage	12-30 VDC
Wetted Parts	Polycarbonate
Electrical Connection	EN 175301-803-A connector
IP Rating	IP65
NEMA Rating	4X
IO-Link Compatible	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	053988_C_000
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/FTI26-CA4VWDG.pdf>
See store item page for other formats.