

FTI26-CO4NWDJ Cut Sheet



Endress+Hauser Nivector capacitance bulk solids level switch, 316L stainless steel, ECTFE wetted parts, G1 male thread process connection, switch PNP, 3-wire, N.O./N.C. complementary, 4-pin M12 quick-disconnect, IP66 IP68 IP69 (NEMA 4X/6P).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FTI26-CO4NWDJ>

Technical Specifications

Brand	Endress+Hauser
Item	Level switch
Series	Nivector
Sensor Type	Capacitance
Media Type	Bulk solids
Mounting	Any orientation
Insertion Length	2.84in/72mm
Process Connection	G1 male thread

Process Temperature	-4 to 167 deg F
Output	Switch PNP, 3-wire, N.O./N.C. complementary
Operating Voltage	12-30 VDC
Wetted Parts	316L stainless steel, ECTFE
Electrical Connection	4-pin M12 quick-disconnect
Housing Rating	IP66 IP68 IP69 (NEMA 4X/6P)
Application	Hazardous location rated
IO-Link Compatible	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	053988_C_000
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	3-A Certification/CSA Control Drawing

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/FTI26-CO4NWDJ.pdf>
See store item page for other formats.