

FTM20-AM23A Cut Sheet



Endress+Hauser Soliphant vibration rod bulk solids level switch, polyester housing, 8.86in insertion length, 316L stainless steel wetted parts, 1-1/4in male NPT process connection, switch PNP, 3-wire, N.O./N.C. selectable, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FTM20-AM23A>

Technical Specifications

Brand	Endress+Hauser
Item	Level switch
Series	Soliphant
Sensor Type	Vibration rod
Media Type	Bulk solids
Mounting	Any orientation
Insertion Length	8.86in
Process Connection	1-1/4in male NPT

Process Temperature	-40 to 302 deg F
Output	Switch PNP, 3-wire, N.O./N.C. selectable
Operating Voltage	10-45 VDC
Wetted Parts	316L stainless steel
Electrical Connection	Screw terminals
Housing Material	Polyester
IP Rating	IP66 and IP67
NEMA Rating	4X

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/FTM20-AM23A.pdf>
See store item page for other formats.