

FTM20-CN46A Cut Sheet



Endress+Hauser Soliphant vibration rod bulk solids level switch, aluminum housing, 8.86in insertion length, 316L stainless steel wetted parts, 1-1/2in male NPT process connection, DPDT relay, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FTM20-CN46A>

Technical Specifications

Brand	Endress+Hauser
Item	Level switch
Series	Soliphant
Sensor Type	Vibration rod
Media Type	Bulk solids
Mounting	Any orientation
Insertion Length	8.86in
Process Connection	1-1/2in male NPT

Process Temperature	-40 to 302 deg F
Output	DPDT relay
Operating Voltage	19-253 VAC and 19-55 VDC
Wetted Parts	316L stainless steel
Electrical Connection	Screw terminals
Housing Material	Aluminum
IP Rating	IP66 and IP67
NEMA Rating	4X

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	053988_C_000
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/FTM20-CN46A.pdf>
See store item page for other formats.