

# FTS200-1002 Cut Sheet



ProSense liquid or air flow sensor, thermal, 200mm probe length, liquid: 0.15 to 9.85 ft/sec, air: 6 to 328 ft/sec, -4 to 212 F, Output: analog, Output 2: analog, 18 to 30 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FTS200-1002>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Flow sensor
<b>Media Type</b>	Liquid or air
<b>Sensing Type</b>	Thermal
<b>Measuring Range</b>	Liquid: 0.15 to 9.85 ft/sec, air: 6 to 328 ft/sec
<b>Measuring Range 2</b>	-4 to 212 F
<b>Output</b>	Analog, 4-20 mA
<b>Output 2</b>	Analog, 4-20 mA
<b>Operating Voltage</b>	18 to 30 VDC
<b>Electrical Connection</b>	4-pin M12 quick-disconnect
<b>Additional Information</b>	Purchase cable and mounting fitting separately

## Agency Approvals

<b>UL Listed File #</b>	E320431
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>