

FTW23-CA4MWVJ Cut Sheet



Endress+Hauser Liquipoint capacitance liquid level switch, 316L stainless steel, peek wetted parts, G1/2 male thread process connection, switch PNP, 3-wire, N.O./N.C. complementary, 4-pin M12 quick-disconnect, IP65 IP67 (NEMA 4X).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FTW23-CA4MWVJ>

Technical Specifications

Brand	Endress+Hauser
Item	Level switch
Series	Liquipoint
Sensor Type	Capacitance
Media Type	Liquid
Mounting	Any orientation
Insertion Length	13mm (0.51in)
Process Connection	G1/2 male thread

Process Temperature	-4 to 212 deg F
Output	Switch PNP, 3-wire, N.O./N.C. complementary
Operating Voltage	10-30 VDC
Wetted Parts	316L stainless steel, peek
Electrical Connection	4-pin M12 quick-disconnect
Housing Rating	IP65 IP67 (NEMA 4X)
IO-Link Compatible	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	053988_C_000
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/FTW23-CA4MWVJ.pdf>
See store item page for other formats.