

FVR10M-14R Cut Sheet



NITRA pneumatic push-to-connect fitting, elbow flow control valve, rotating, meter-in, thermoplastic (PBT) body, nickel-plated brass threads, 10mm tube to R1/4 BSPT connection(s). Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FVR10M-14R>

Technical Specifications

| | |
|------------------------------|------------------------------------|
| Brand | NITRA |
| Item | Pneumatic Push-to-connect Fitting |
| Fitting Type | Elbow flow control valve |
| Fitting Function | Rotating |
| Valve Function | Meter-in |
| Body Material | Thermoplastic (PBT) |
| Thread Material | Nickel-plated brass |
| Thread Sealant | Yes |
| Connection | 10mm push-to-connect and R1/4 BSPT |
| Operating Pressure | -29.5in Hg to 150 psi |
| Operating Temperature | 32 to 140 deg F |
| Quantity per Pack | 2 |
| For Use With | Flexible pneumatic tubing |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |